


# BALLSCREW BEARINGS



## Product Features

- Excellent axial rigidity.
- Excellent tolerance control supports flexible bearing arrangement combinations for custom application requirements.
- HIWIN provides complete solution services, including bearings combined with HIWIN ballscrews.

## Product Specification



## Standard BSB dimensional tolerances

Unit:  $\mu\text{m}$

Nominal Bearing I.D. or O.D. (mm)		Inside diameter deviations		Outside diameter deviations		Deviations of width		Outer or inner ring axial run out
		$\Delta_{dmp}$		$\Delta_{Dmp}$		$\Delta_{Bs}$		$S_{ea}, S_{ia}$
Over	Include	Upper Limit	Lower Limit	Upper Limit	Lower Limit	Upper Limit	Lower Limit	Max
10	18	0	-4	-	-	0	-80	2.5
18	30	0	-5	-	-	0	-120	2.5
30	50	0	-6	0	-6	0	-120	2.5
50	80	0	-7	0	-7	0	-150	2.5
80	120	0	-8	0	-8	0	-200	2.5


## Standard shaft diameter and bearing bore dimensional tolerance

Unit:  $\mu\text{m}$

Shaft dia./ Bearing bore dimension (mm)		Tolerance of shaft dia.		Tolerance of bearing bore	
		h5		H6	
Over	Include	Upper Limit	Lower Limit	Upper Limit	Lower Limit
10	18	0	-8	-	-
18	30	0	-9	-	-
30	50	0	-11	+16	0
50	80	0	-13	+19	0
80	120	0	-15	+22	0




## Bearing specification table



Specification			Main dimensions (mm)				
Open type	with dust proof cap (contact type)	with dust proof cap (non-contact type)	d	D	B	r(min)	$r_1$ (min)
15 BSB 47	15 BSB 47 WW	15 BSB 47 UU	15	47	15	1	0.6
17 BSB 47	17 BSB 47 WW	17 BSB 47 UU	17	47	15	1	0.6
20 BSB 47	20 BSB 47 WW	20 BSB 47 UU	20	47	15	1	0.6
25 BSB 62	25 BSB 62 WW	25 BSB 62 UU	25	62	15	1	0.6
30 BSB 62	30 BSB 62 WW	30 BSB 62 UU	30	62	15	1	0.6
35 BSB 72	35 BSB 72 WW	35 BSB 72 UU	35	72	15	1	0.6
40 BSB 72	40 BSB 72 WW	40 BSB 72 UU	40	72	15	1	0.6



## Single bearing calculated rigidity chart




	Basic dynamic load rating (Note1)	Max axial load (Note2)	Shaft diameter (mm)	Allowable speed (rpm)	Other dimensions (mm)			
	Ca (kN)	C <sub>0a</sub> (kN)			d <sub>1</sub>	d <sub>2</sub>	D <sub>1</sub>	D <sub>2</sub>
	21.9	26.6	Ø20	6000	27.3	34	34.2	39.6
	21.9	26.6	Ø25-Ø28	6000	27.3	34	34.2	39.6
	21.9	26.6	Ø25-Ø28	6000	27.3	34	34.2	39.6
	29.2	43	Ø30-Ø36	4300	39.6	47.2	47.5	53.3
	29.2	43	Ø40	4300	39.6	47.2	47.5	53.3
	31.5	52	Ø45	3600	49.3	57.1	57.4	63.2
	31.5	52	Ø50	3600	49.3	57.1	57.4	63.2

Note: 1.For the axial load capacity of multiplex arrangements, please refer to the basic dynamic load rating in the "Bearing performance" table.  
2.In applications with multiplex arrangements, the value in this table will be multiplied accordingly.



## Assembly arrangement



## Bearing performance by assembly arrangement


Spec.	Bearing assembly type						
	Duplex DF, DB			Triplex DFD, DBD			
	Preload (kN)	Stiffness (kN/ $\mu$ m)	Start torque (N.cm)	Preload (kN)	Stiffness (kN/ $\mu$ m)	Start torque (N.cm)	
15 BSB 47	2.1	0.75	14	2.9	1.1	20	
17 BSB 47	2.1	0.75	14	2.9	1.1	20	
20 BSB 47	2.1	0.75	14	2.9	1.1	20	
25 BSB 62	3.3	1.0	24	4.5	1.5	33	
30 BSB 62	3.3	1.0	24	4.5	1.5	33	
35 BSB 72	3.9	1.2	28	5.3	1.8	37	
40 BSB 72	3.9	1.2	28	5.3	1.8	37	

## Dynamic equivalent load

$$P_a = X F_r + Y F_a$$

Assembly row Assembly arrangement Load carrying row(s) $e=2.17$		Duplex		Triplex			Quadruplex		
		DB/ DF	DT	DBD/ DFD		DTD	DFT	DFF	DFT
		1 row	2 rows	1 row	2 rows	3 rows	1 row	2 rows	3 rows
$F_a/F_r \leq e$	X	1.9	-	1.43	2.33	-	1.17	2.33	2.53
	Y	0.54	-	0.77	0.35	-	0.89	0.35	0.26
$F_a/F_r > e$	X	0.92	0.92	0.92	0.92	0.92	0.92	0.92	0.92
	Y	1	1	1	1	1	1	1	1

## Dust proof cap comparison



\*Tested bearings: 30 BSB 62, DF design, RPM 1800min<sup>-1</sup>

Bearing assembly type				Basic dynamic load rating (kN)		
Preload (kN)	Stiffness (kN/μm)	Start torque (N.cm)	Quadruplex DFF, DBB			
			supported by 1 row	supported by 2 rows	supported by 3 rows	
			Single row, DF, DB	DT, DBD, DFD, DBB, DFF	DTD, DFT, DBT	
4.3	1.4	29	21.9	35.5	47.5	
4.3	1.4	29	21.9	35.5	47.5	
4.3	1.4	29	21.9	35.5	47.5	
6.6	2.0	49	29.2	47.5	63	
6.6	2.0	49	29.2	47.5	63	
7.8	2.4	55	31.5	51.5	68.5	
7.8	2.4	55	31.5	51.5	68.5	

## Subsidiaries / Research Center

---

**HIWIN GmbH**  
OFFENBURG, GERMANY  
www.hiwin.de  
www.hiwin.eu  
info@hiwin.de

**HIWIN JAPAN**  
KOBE · TOKYO · NAGOYA · NAGANO ·  
TOHOKU · SHIZUOKA · HOKURIKU ·  
HIROSHIMA · FUKUOKA · KUMAMOTO,  
JAPAN  
www.hiwin.co.jp  
info@hiwin.co.jp

**HIWIN USA**  
CHICAGO, U.S.A.  
www.hiwin.com  
info@hiwin.com

**HIWIN Srl**  
BRUGHERIO, ITALY  
www.hiwin.it  
info@hiwin.it

**HIWIN Schweiz GmbH**  
JONA, SWITZERLAND  
www.hiwin.ch  
info@hiwin.ch

**HIWIN s.r.o.**  
BRNO, CZECH REPUBLIC  
www.hiwin.cz  
info@hiwin.cz

**HIWIN SINGAPORE**  
SINGAPORE  
www.hiwin.sg  
info@hiwin.sg

**HIWIN KOREA**  
SUWON · MASAN, KOREA  
www.hiwin.kr  
info@hiwin.kr

**HIWIN CHINA**  
SUZHOU, CHINA  
www.hiwin.cn  
info@hiwin.cn

**Mega-Fabs Motion**  
Systems, Ltd.  
HAIFA, ISRAEL  
www.mega-fabs.com  
info@mega-fabs.com

# HIWIN®

## HIWIN TECHNOLOGIES CORP.

No. 7, Jingke Road,  
Taichung Precision Machinery Park,  
Taichung 40852, Taiwan  
Tel: +886-4-23594510  
Fax: +886-4-23594420  
www.hiwin.tw  
business@hiwin.tw

- 
- HIWIN is a registered trademark of HIWIN Technologies Corp. For your protection, avoid buying counterfeit products from unknown sources.
  - Actual products may differ from specifications and photos provided in this catalog. These differences may be the result of various factors including product improvements.
  - HIWIN will not sell or export products or processes restricted under the "Foreign Trade Act" or related regulations. Export of restricted products should be approved by proper authorities in accordance with relevant laws and shall not be used to manufacture or develop nuclear, biochemical, missiles or other weapons.
  - HIWIN website for patented product directory: [http://www.hiwin.tw/Products/Products\\_patents.aspx](http://www.hiwin.tw/Products/Products_patents.aspx)

The specifications in this catalog are subject to change without notification.

Copyright © HIWIN Technologies Corp.

©2018 FORM B02DE04-1809 (PRINTED IN TAIWAN)